WAVEN PTY LTD









Powerful Functions of WAVEN MOBILITY SCOOTER

- 1. Folding Function
- 2. Displaying Remaining Charge in Numeric Values
- 3. Powerful HUB Motor (BLDC) & Battery (24V 30A Lithiumion battery)
- 4. Regenerative Braking
- 5. Cruising Function
- 6. Automatic speed reduction system for rotation and reverse
- 7. Front and Rear suspension







HEADLAX A detachable headrest for wheelchair

A: Adaptable for all wheelchairs (38 to 51cm wide).

B: Height can be adjusted to fit the user's height.


C: It's equipped with a IV pole holder for comfortable use. High-end anti-bacterial bio-chip pillow provides hygienic and comfortable head support.

Product composition


① Pillow: 1EA,

② Support fixture: 2EA ③ Pillow support: 2EA,


4 Support connection pipe : 1EA5 Wrench : 1EA, User's guide : 1Shee








The Portable IV holder can be used by attaching right/left bidirectional attachments to the wheelchair. No need to drill the wheelchair when you fabricate the holder to the wheelchair. You can just use a wrench









This unique Spoke Guard design will let users demonstrate their individuality by expressing their source of independence to challenge negative associations of wheelchairs. It makes the uniform wheelchair unique by attaching the spoke guard of wheels. You can customize your whe elchair to express your personality.

Product composition Spoke Guards : 2EA,

Zip ties : 6EA,

User's guide: 1Sheet







Australian Government Department of Health TGA Certificate [Mobility Scooter]



Many eyes are surprisingly impressed with our Products



On Off-line Customer Satisfaction Program Strengthen customer support through CSUS (Customer Satisfaction Up System)



Made in KOREA [All Product]



Superior technology We leads the market with "Creative Business Model" through various convergence in all areas of Medicare Industry



Patent Products

About Universal Fever Screening Camera



- Effective pixels 384 x 288 / NETD < 50mK
- 9.7 mm fixed lens Accuracy $\pm 0.3^{\circ}$ C with black body
- Optimized body heat measurement 20 ~ 40 oC Visible Camera
- Full HD 1920x1080 resolution
- 6mm fixed lens Function
- Dedicated fever screening system (HW/SW)
- Super easy to install and configure (Plug & Play)
- Simple and powerful operation software
- Competitive Total Cost of Ownership design
- Friendly user experience consideration
- Max. 10 people simultaneous fever screening
- Alarming function when detecting abnormality
- Al based face detection to reduce false alarm.



Hire a WAVEN GILBOT V1 Mobility Scooter

Hire a WAVEN GILBOT V1 Mobility Scooter. Minimum hire period of two weeks. Initial hire period of four-weeks with all unused weeks refunded when the scooter is returned. *Model & Color of hire items may vary depending on availability





Black or Red-WINE

- Made in KOREA
- Australian Government Department of Health TGA Certificate Motorised Wheelchair





about us

WAVEN Pty Ltd is a global Medicare market leader and a leading provider of Medicare products that strive to create a new life for a convenient wellness society. We are striving to become a global leader in creating and supplying the best Medicare products to build a better well-being society through new Medicare technology and cutting-edge product supply.



Contact: 0434 003 790 [Daniel Ko]

www.waven.com.au / Tel: 02-8789-1773 | 1300 736 530

Ware House: HYUNDAI GLOVIS 2/147 Newton Road, Wetherill Park, NSW 2164